



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	a	b	h <sub>1</sub>	h <sub>2</sub> ≈	Length l ≈
16	M 8	7	12	12	35	56
20	M 10	9	14	14	44	70
25	M 12	11	18	18	52	87
32	M 16	15	22	22	66	109
40	M 20	18	28	28	84	140

**Specification**

- Malleable cast iron —
  - Fettle
  - Contact faces machined
- Stainless steel precision casting AISI CF-8 **NI**
  - Fettle
  - Contact faces machined
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**On request**

- Clamp nuts GN 206, powder coated

**Information**

- see also...
- *Clamp Nuts GN 99.5 (Steel, Zinc Plated)* → Page 506
  - *Stainless Steel Clamp Nuts GN 99.6* → Page 506

How to order (Steel) <sup>1</sup> <sup>2</sup> <b>GN 206-32-M16</b>	1	d <sub>1</sub>
	2	d <sub>2</sub>

How to order (Stainless steel) <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>GN 206-25-M12-NI</b>	1	d <sub>1</sub>
	2	d <sub>2</sub>
	3	Material