



EDELSTAHL®
Rostfrei
Inox
Stainless
Steel

- 4 Type (Base plate)**
- D0** Fine turned, without rubber pad
 - D1** Fine turned, with rubber pad, inlaid, black

d ₁	d ₂	l ₁						l ₂						l ₃ ≈				l ₇	k		
		Version S / SK			Version T / TK und U / UK			Version V / VK			Version W				Version X						
80	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	34	54,5
80	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	37	54,5
80	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	40	54,5
80	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	118	143	168	193	46	54,5
80	M 20	-	-	-	-	75	100	125	150	200	250	100	125	150	200	143	168	193	243	54	54,5
80	M 24	-	-	-	-	100	125	150	200	300	-	100	150	200	-	168	218	268	-	-	54,5
100	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	35	70,5
100	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	38	70,5
100	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	41	70,5
100	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	119	144	169	194	47	70,5
100	M 20	-	-	-	-	75	100	125	150	200	250	100	125	150	200	144	169	194	244	55	70,5
100	M 24	-	-	-	-	100	125	150	200	300	-	100	150	200	-	169	219	269	-	-	70,5
120	M 20	-	-	-	-	75	100	125	150	200	250	-	-	-	-	-	-	-	-	59	95,5
120	M 24	-	-	-	-	100	125	150	200	300	-	-	-	-	-	-	-	-	-	-	95,5
120	M 30	-	-	-	-	100	125	150	200	300	-	-	-	-	-	-	-	-	-	-	95,5

Specification

- Base plate
Stainless steel AISI 304
- Threaded stem
Stainless steel AISI 303
- Hex nut ISO 4032
Stainless steel AISI 304
- Rubber pad, inlaid
NBR (Perbunan®), 70 Shore A
- *Load Rating Information* → Page 2146
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Leveling feet GN 21 / GN 23 will be delivered mounted and are not removable.

see also...

- *Stainless Steel Leveling Feet GN 31* → Page 1478
- *Stainless Steel Leveling Feet GN 41* → Page 1462

How to order (Without mounting holes)

1	d ₁
2	d ₂
3	l ₇ (l ₁ , l ₂ , l ₃)
4	Type (Base plate)
5	Version (Stem)

1
2
3
4
5

GN 21-100-M20-55-D1-X

How to order (With mounting holes)

1	d ₁
2	d ₂
3	l ₁ (l ₂ , l ₃ , l ₇)
4	Type (Base plate)
5	Version (Stem)

1
2
3
4
5

GN 23-80-M10-50-D0-S

Versions of threaded stem

<p>5 S Without nut SK With nut</p>	<p>5 T Without nut TK With nut</p>	<p>5 U Without nut UK With nut</p>
<p>External hex at the bottom at d_2 M 8, M 10, M 12</p>	<p>Wrench flat at the bottom at d_2 M 16, M 20, M 24, M 30</p>	<p>Hex socket at the top and wrench flat at the bottom at d_2 M 16, M 20, M 24, M 30</p>
<p>5 V Without nut VK With nut</p>	<p>5 W With adjustable sleeve Adjustable range</p>	<p>5 X With internal thread</p>
<p>External hex at the top and wrench flat at the bottom at d_2 M 16, M 20, M 24</p>	<p>Covered thread and wrench flat at the bottom at d_2 M 16, M 20, M 24</p>	<p>External hex with internal thread at d_2 M 8, M 10, M 12, M 16, M 20</p>

d_1	d_2	d_3	h_1	h_2	h_3	h_4	h_5	l_4	l_5	l_6	A/F ₁	A/F ₂	A/F ₃	A/F ₄	A/F ₅	A/F ₆	A/F ₇	t
80	M 8	-	8,5	2	19,5	-	-	-	-	-	17	-	-	-	-	-	14	8
80	M 10	-	8,5	2	19,5	-	-	-	-	-	17	-	-	-	-	-	14	10
80	M 12	-	8,5	2	19,5	-	-	-	-	-	17	-	-	-	-	-	17	12
80	M 16	24	8,5	2	-	25,5	21,5	45	45	29	-	12	8	10	12	20	22	16
80	M 20	30	8,5	2	-	27	23	56	56	36	-	15	10	13	16	24	27	20
80	M 24	35	8,5	2	-	30,5	26	67	67	42	-	19	12	17	20	30	-	-
100	M 8	-	9	3	20,5	-	-	-	-	-	17	-	-	-	-	-	14	8
100	M 10	-	9	3	20,5	-	-	-	-	-	17	-	-	-	-	-	14	10
100	M 12	-	9	3	20,5	-	-	-	-	-	17	-	-	-	-	-	17	12
100	M 16	24	9	3	-	26,5	22,5	45	45	32	-	12	8	10	12	20	22	16
100	M 20	30	9	3	-	28	24	56	56	40	-	15	10	13	16	24	27	20
100	M 24	35	9	3	-	31,5	27	67	67	48	-	19	12	17	20	30	-	-
120	M 20	-	12	3,5	-	32	-	-	-	-	-	15	10	-	-	-	27	20
120	M 24	-	12	3,5	-	35,5	-	-	-	-	-	19	12	-	-	-	-	-
120	M 30	-	12	3,5	-	39,5	-	-	-	-	-	24	12	-	-	-	-	-

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

