



1	2	3											
l_1	d_1	l_2	d_2	d_3	d_4	h_1	h_2	h_3	h_4	Stroke			
63	M 6	12	16	20	25	32	14	14,8	19	43,8	16,3	60,1	2,5
63	M 8	12	16	20	25	32	18	18,8	19	45,8	18,3	62,1	2,5
78	M 8	12	16	20	25	32	18	18,8	24	49,3	16,5	69,3	3
78	M 10	16	20	25	32	-	22	22,8	24	51,3	18,5	71,3	3

Specification

Handle

Stainless steel
precision casting AISI 316
Polished finish (Ra < 0.8 µm)

PL

Insert

Stainless steel AISI 304

Sealing ring / Wiper

- HNBR H
- Temperature resistant -25 °C to + 150 °C
- EPDM E
- Temperature resistant -40 °C to + 120 °C
- FDA compliant material
- Blue
- Hardness 85±5 Shore A

RoHS

Adjustable hand levers GN 305 with solid stainless steel handle comply with the DGUV testing principles, making them suitable for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the impervious exterior surfaces prevent adherence of dirt and facilitate cleaning.

Adjustable hand levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is moveably attached to the handle with serrations. When pulling the handle, the serration frees itself and can be re-located into any required position. Engagement is achieved by releasing the lever.

see also...

	Page
GN 5435 Star Knobs (Hygienic Design)	QVX
GN 5445 Three-Lobed Knobs (Hygienic Design)	QVX

Technical Information

Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 7600 Sealing Rings	QVX
-----------------------	-----

Security Information

The information in the operating instruction must be observed during installation, initial operation, and use. It is enclosed with the product and is provided digitally on the product page at ganternorm.com.

How to order

1	l_1
2	d_1
3	l_2
4	Oberfläche
5	Material (Sealing ring)

GN 305-78-M10-20-PL-E

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

