



ROSTFREI  
Inox  
Stainless  
Steel

**4 Type**  
E Angled lever

1 2 3

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>		d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	h <sub>1</sub>	h <sub>3</sub>	h <sub>4</sub> ≈	h <sub>5</sub> Stroke	l <sub>2</sub> ≈	l <sub>3</sub> ≈					
21	M 8	16	20	25	32	40	50	63	13,5	8	20	33,5	1	59	4	75	70
24	M 10	20	25	32	40	50	63	80	16	10	25	40	2,5	75	4,5	101	96
28	M 12	25	32	40	50	63	80	-	19	12	30	48,5	4,5	89	4,5	116	110

### Specification

- Stainless steel AISI 303  
Matte shot-blasted
- Ball knobs DIN 319  
Plastic, Duroplast  
Black, shiny finish
- Safety circlip  
Plastic (Polyacetal POM)
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

### On request

- Straight lever (90°)
- With inch threads

### Information

Adjustable tension levers GN 212.5 have proved to be ideal whenever parts have to be clamped in a confined space or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

- Adjustable Tension Levers GN 212.3 (Steel, Blackened) → Page 481

How to order

1	d <sub>1</sub>
2	d <sub>2</sub>
3	l <sub>1</sub>
4	Type

GN 212.5-28-M12-25-E

