


Application example



| ¹ l ₁ | ² d ₁ | d ₂ | d ₃ | d ₄ | h ₁ | h ₂ | h ₃ | h ₄ Stroke | s | t min. |
|-----------------------------|-----------------------------|----------------|----------------|----------------|----------------|----------------|----------------|--------------------------|-----|-----------|
| 30 | M 5 | 13 | 10 | 13 | 24,5 | 4 | 31 | 3,5 | 2,5 | 10 |
| 45 | M 6 | 15 | 10 | 13 | 24,5 | 4 | 34 | 3,5 | 3 | 10 |
| 63 | M 8 | 20 | 13,5 | 17,5 | 31 | 6,5 | 45 | 4 | 3,5 | 13 |
| 78 | M 10 | 25 | 16 | 21 | 36 | 8 | 54 | 4 | 4 | 16 |

Specification

Handle

Zinc die casting
Powder coated

- Black, RAL 9005, textured finish
- Orange, RAL 2004, textured finish
- Red, RAL 3000, textured finish
- Silver, RAL 9006, textured finish

- SW
- OS
- RS
- SR

Insert / Retaining screw

Steel, blackened
property class 5.8

Washer

- Steel
- Case-hardened
- Blackened

RoHS

Adjustable hand levers GN 307 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. On releasing the handle the serrations re-engage automatically.

When pulling the handle, the serration frees itself and can be re-located into any required position. Engagement is achieved by „releasing“ the lever.

The washer cannot be removed and does not turn when the lever is actuated. It protects the clamped surface from damage. One typical application is to use the hand lever for slotted holes.

see also...

| | Page |
|---|------|
| GN 300 Adjustable Hand Levers (without washer) | QVX |
| GN 300.4 Adjustable Hand Levers (with increased clamping force) | QVX |
| GN 303 Adjustable hand levers (with push button) | QVX |

How to order

GN 307-63-M8-SW

- ¹ l₁
- ² d₁
- ³ Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

