


Pawl retracted

**Application example**



d <sub>1</sub>	l <sub>1</sub> +0,4 Minimum size											a	b	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	l <sub>2</sub>	l <sub>3</sub>				
6	10*	12*	16	20	25	30	35	40	45	50	60	70	80	-	-	2,3	0,5	7,5 +0,5	5,9	12	23	7	38
8	10*	16	20	25	30	35	40	45	50	60	70	80	90	100	-	2,8	0,6	10 +0,5	7,9	12	23	8,4	38
10	15	20	25	30	35	40	45	50	60	70	80	90	100	110	120	3,3	1	12 +1	9,9	16	28	9,8	42
12	20	25	30	35	40	45	50	60	70	80	90	100	110	120	-	3,8	1	14 +1	11,9	16	28	11,3	42
16	30	35	40	45	50	60	70	80	90	100	110	120	130	140	150	4,8	1,2	19 +1	15,9	20	32	14,2	46,5

\* only GN 214.3

**Specification**

**GN 214.3**

- Pin  
Stainless Steel AISI 303
- Slide / Push button  
Plastic  
temperature resistant up to 80 °C  
red

**GN 214.6**

- Pin  
Stainless Steel AISI 303
- Slide / Push button  
Stainless Steel AISI 303

This information applies to both standards:

- Pawl  
Stainless Steel sheet metal AISI 304
- Lifting ring  
Stainless Steel AISI 301
- Spring  
Stainless Steel AISI 301
- Load capacity → Page XYZ
- Stainless Steel characteristics → Page 1489
- Plastic characteristics → Page 1483
- RoHS

**Accessory**

- Ball chains GN 111 / GN 111.5 → Page 876
- Retaining cables GN 111.2 → Page 877
- Spiral retaining cables GN 111.4 → Page 878

**Information**

Stainless Steel-Locking pins with axial lock GN 214.3 / GN 214.6 are used for quick fixing, connecting and locking of various jig and fixture systems. A typical application is location pins which have to be often removed and re-placed again.

The rectangular pawls made of Stainless Steel sheet metal keep the locking pin in an axial position in the bore. It can be retracted by pressing the button, once released it returns the pressure spring into its locking position.

The version with swivelling lifting ring is ideal for the use in confined spaces.

The technical annexe contains the load capacities for the double-sided shearing resistance (breaking strength).

see also...

- List of lock pin types → Page 746 ff.
- Stainless Steel-Locking pins GN 114.3 (with knob) → Page 753
- Guide bushings DIN 172 (cylindrical, with collar) → Page 683
- Guide bushings DIN 179 (cylindrical, without collar) → Page 683

How to order (Stainless Steel, with plastic slide)	1	d <sub>1</sub>
<b>GN214.3-16-70</b>	2	l <sub>1</sub>

How to order (Stainless Steel, with St. Steel slide)	1	d <sub>1</sub>
<b>GN214.6-10-60</b>	2	l <sub>1</sub>