



4 Type

- C** with tapped hole, no bushing
- E** with tapped bushing

d₁	d₂		KT		d₃		d₄ ≈	h ≈	t₁ min.	t₂ min.		
	KU	Type C	Thread	Type C	Thread	KU	Type E	Thread				
10	M 3	-	-	-	-	-	-	-	5	9,3	6	-
12	M 4	-	-	-	-	-	-	-	6	11,2	6	-
16	M 4	M 5	-	M 4	M 5	M 4**	-	-	8	15	6	6
20	M 5	M 6	-	M 5	M 6	M 5	-	M 5	12	18	7,5	7,5
25	M 5	M 6	M 8	M 6	M 8	M 6	M 8*	M 6	15	22,5	9	9
30	M 8	-	-	-	-	-	-	-	15	28	12	-
32	M 6	M 8	M 10	M 8	M 10	M 8	-	M 8	18	29	12	12
35	M 10	-	-	-	-	-	-	-	18	32,5	15	-
40	M 8	M 10	M 12	M 10	M 12	M 10	-	-	22	37	15	15
50	M 12	-	-	-	-	M 12	-	-	28	46	18	18

* This size is only available in black with bushing in steel. ** This size is only available in black with bushing in brass.

Specification

- Plastic **KU**
 - Duroplast (Phenolic PF)
 - Flash removed and polished
 - black (standard color) —
 - red, similar RAL 3003 ● **RT**
- Bushing (Type E)
 - Steel, zinc plated (standard)
 - Brass **MS**
- Plastic **KT**
 - Technopolymer (Polyamide PA)
 - Flash removed and polished
 - black, matte (standard color) —
 - red, similar RAL 3000 ● **RT**
- Bushing (Type E)
 - Steel, zinc plated
- *Plastic characteristics* → Page 1483
- **RoHS**

Information

Ball knobs DIN 319 in sizes 30 and 35, as well as various thread of type C and ball knobs made of technopolymer (KT) are not on the official DIN standard sheet.

see also...

- *Ball knobs, Press on type DIN 319* → Page 48

How to order (black, with bushing steel)

1	Material
2	d₁
3	d₂ (d₃)
4	Type

DIN 319-KU-25-M6-C

How to order (red, with bushing steel)

1	Material
2	d₁
3	d₂ (d₃)
4	Type
5	Color

DIN 319-KT-32-M8-C-RT

How to order (black, with bushing brass)

1	Material
2	d₁
3	d₃
4	Type
5	Bushing

DIN 319-KU-25-M6-E-MS