



**Versions of threaded stem**

<p><b>S</b> Without nut <b>SK</b> With nut</p>	<p><b>T</b> Without nut <b>TK</b> With nut</p>	<p><b>U</b> Without nut <b>UK</b> With nut</p>
<p>External hex at the bottom at <math>d_2</math> M 8, M 10, M 12</p>	<p>Wrench flat at the bottom at <math>d_2</math> M 16, M 20, M 24</p>	<p>Hex socket at the top and wrench flat at the bottom at <math>d_2</math> M 16, M 20, M 24</p>

<p><b>V</b> Without nut <b>VK</b> With nut</p>	<p><b>W</b> With adjustable sleeve</p> <p>Adjustable range Adjustable sleeve</p>	<p><b>X</b> With internal thread</p>
<p>External hex at the top and wrench flat at the bottom at <math>d_2</math> M 16, M 20, M 24</p>	<p>Covered thread and wrench flat at the bottom at <math>d_2</math> M 16, M 20, M 24</p>	<p>External hex with internal thread at <math>d_2</math> M 8, M 10, M 12, M 16, M 20</p>

$d_1$	$d_2$		$d_3$	$d_4$	$h_1$	$h_3$	$h_4$	$h_5$	$l_4$	$l_5$	$l_6$	$l_8$	$l_9$	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>4</sub>	A/F <sub>5</sub>	A/F <sub>6</sub>	
50	M 8	M 10	M 12	-	13	18	26	-	-	-	-	25	45	17	-	-	-	-	-	
50	M 16	-	-	-	13	18	-	32	-	-	-	25	45	-	12	8	-	-	-	
60	M 8	M 10	M 12	-	13	19	27	-	-	-	-	25	50	17	-	-	-	-	-	
60	M 16	-	-	24	13	19	-	33	30	45	45	29	25	50	-	12	8	10	12	20
80	M 8	M 10	M 12	-	13	20	28	-	-	-	-	30	70	17	-	-	-	-	-	
80	M 16	-	-	24	13	20	-	34	31	45	45	29	30	70	-	12	8	10	12	20
80	M 20	-	-	30	13	20	-	35	32	56	56	36	30	70	-	15	10	13	16	24
80	M 24	-	-	35	13	20	-	38	35	67	67	42	30	70	-	19	12	17	20	30
100	M 8	M 10	M 12	-	13	21	29	-	-	-	-	30	80	17	-	-	-	-	-	
100	M 16	-	-	24	13	21	-	35	32	45	45	29	30	80	-	12	8	10	12	20
100	M 20	-	-	30	13	21	-	36	33	56	56	36	30	80	-	15	10	13	16	24
100	M 24	-	-	35	13	21	-	39	36	67	67	42	30	80	-	19	12	17	20	30

**Information**

Leveling feet GN 33 will be delivered mounted and are not removable.

• Load Rating Information → Page 2143

see also...

- Leveling Feet GN 32 (Steel, Zinc Plated) → Page 1480
- Leveling Feet GN 31 (without Flange) → Page 1478
- Insert Bushings GN 448 (for Tubes) → Page 1498 / 1499

<p>How to order</p> <p><b>GN33-60-M16-100-B1-V</b></p>	1	$d_1$
	2	$d_2$
	3	$l_1$ ( $l_2, l_3, l_7$ )
	4	Type (Base plate)
	5	Version (Stem)