




elesa
Original design I.149



¹ d ₁	² d ₂	³ l ₁	d ₃	l ₂ min.	l ₃ ±0,5	l ₄ ≈
34	M 10	67	19	40	8	24
34	M 10	86	20	48	7	25

Specification

Plastic, phenolic resin (PF)

- Operating temperature -20 °C to +110 °C
- Black, shiny finish

RoHS

When using the tapered knobs GN 219, make sure that the threaded pin is sufficiently long. Otherwise the plastic element may break under excessive stress exposure.

Technical Information

Plastic Characteristics

Page

QVX

How to order

¹ ² ³
GN 219-34-M10-67

1	d ₁
2	d ₂
3	l ₁