



¹ d ₁	² Length l	b ₁	b ₂	b ₃	b ₄	d ₂	h ₁	h ₂	t min.
28	200 250 300 400 500 600	25	14	50	66	M 8	50	66	15

Specification

Handle tube

Stainless steel AISI 304, wall thickness 2 mm
Ground, matte shiny finish

Handle legs

Stainless steel precision casting AISI CF-8
Matte shot-blasted

RoHS

With the tubular handles GN 333.6, the handle legs and the handle tube are pressed together.

A typical application for tubular handles is on double-winged doors for machines or devices.

see also...

	Page
GN 333.7 Tubular Handles (Straight)	QVX
GN 426.5 Cabinet U-Handles	QVX
GN 565.5 Cabinet U-Handles (Mounting from the Back or the Operator's Side)	QVX
GN 666.5 Stainless Steel Tubular Handles (Mounting from the back)	QVX
GN 333 Tubular Handles (Aluminum, Zinc Die Casting)	QVX

Technical Information

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order

GN 333.6-28-250

¹ d ₁
² Length l