



d ₁	d ₂	d ₃	h	Length l ±0,25	t min.
18	M 6	12	42	100	12
20	M 8	14	47	112	15
22	M 10	16	53	125	18
25	M 12	18	59	140	20

Specification

- Cast iron (GS45)
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Plain ○ **BL**
 - Unfinished casting, fettled
- Contact surface machined
- *Load Rating Information* → Page 2106
- **RoHS**



Information

The shape, fastening thread and material all make GN 225 cabinet U-handles highly stable.

see also...

- *Cabinet U-Handles GN 425 (Steel)* → Page 146

How to order

GN 225-20-SW

1	d ₁
2	Finish