



1.1

1.2

1.3

1.4



d ₁	d ₂	d ₃	h	Length l ±0,25	t min.
18	M 6	12	42	100	12
20	M 8	14	47	112	15
22	M 10	16	53	125	18
25	M 12	18	59	140	20

2.1

Specification

- Cast iron (GS45)
 - plastic coated
 - black, RAL 9005, textured finish
 - blank
 - unfinished casting, fettled
- Contact surface machined
- Load rating information → Page XYZ
- RoHS



Information

The shape, fastening thread and material all make GN 225 cabinet U-handles highly stable.

see also...

- Cabinet U-handles GN 425 (Steel) → Page 102

2.2

2.3

2.4

How to order

GN 225-20-SW

1	d ₁
2	Finish

