



**2 Type**

**A** Mounting from the back (threaded blind bore)

**1**

d <sub>1</sub>	d <sub>2</sub>	b <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	b <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	t <sub>min.</sub>
28	M 8	25	14	50	66	50	66	15

**Specification**

**Handle leg**

Zinc die casting  
Powder coated

- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

- **SW**
- **SR**

**Grub screw with plastic pivot**

GN 913.3-M4-6-KU

Steel, blackened

RoHS

**3**

Handle legs GN 333.8 / GN 333.9 can be used for longer tubes or higher loads of tubular handles.

They can be used for tube Ø 28 of the tubular handles GN 333, GN 333.1, GN 333.2 and GN 333.3.

**see also...**

	Page
<b>GN 333</b> Tubular Handles (Angled)	QVX
<b>GN 333.1</b> Tubular Handles (Straight)	QVX
<b>GN 333.2</b> Tubular Handles (Angled, with Movable Handle Legs)	QVX
<b>GN 333.3</b> Tubular Handles (Straight, with Movable Handle Legs)	QVX

How to order (angled version)

**GN 333.8-28-A-SW**

- 1** d<sub>1</sub>
- 2** Type
- 3** Finish

How to order (straight version)

**GN 333.9-28-A-SR**

- 1** d<sub>1</sub>
- 2** Type
- 3** Finish