



1		2		3											
b <sub>1</sub>	l <sub>1</sub> ±0,5								a	b <sub>2</sub>	d	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	t min.
36	200	250	300	350	400	500	600	800	24	22	M 8	57	71	40	15

**Specification**

**Handle tube**

Aluminum

- Powder coated  
Black, RAL 9005, textured finish
- Anodized, natural color  
Handle legs black
- Anodized, natural color  
Handle legs silver

3

● SW

● EL

● ES

**Handle legs**

- Zinc die casting
- Powder coated, textured finish
- Black, RAL 9005 for SW / EL
- Silver, RAL 9006 for ES

**Cover**

Plastic, light gray

RoHS

Oval tubular handles GN 334 are attractive in design and highly stable. The handle tube can be mounted without any further machining, allowing special lengths to be realised easily.

see also...

	Page
GN 333.1 Tubular Handles	QVX
GN 334.1 Oval Tubular Handles (Mounting from the Operator's Side)	QVX
GN 335 Oval Tubular Handles	QVX

**Technical Information**

Load Rating Information	QVX
-------------------------	-----

How to order

1 2 3  
GN 334-36-300-EL

1	b <sub>1</sub>
2	l <sub>1</sub>
3	Finish