



² d	³ s ₀ Square	s ₁ ±0,1	s ₂ ±0,1	l ₁ ±0,5	l ₂	No. of spokes
50	V 6	5,9	6,15	8,5	12	3
50	V 7	6,9	7,15	8,5	12	3
60	V 6	5,9	6,15	8,5	12	3
60	V 7	6,9	7,15	8,5	12	3
70	V 7	6,9	7,15	10	15	3
70	V 8	7,9	8,15	10	15	3
80	V 8	7,9	8,15	11	16	3
80	V 9	8,9	9,15	11	16	3
90	V 9	8,9	9,15	11	16	3
100	V 9	8,9	9,15	13	20	3
100	V 10	9,9	10,15	13	20	3
130	V 12	11,9	12,15	15	23	3

Specification

Pressed steel

- Powder coated
- Black, RAL 9005, matte finish
- Red, RAL 3000, matte finish
- Zinc plated, blue passivated

¹ ⁴
ST

- **SW**
- **RT**
- **ZB**

RoHS

Handwheels GN 227.6 have been specially developed for valves and consist of a single unwelded piece of pressed sheet metal manufactured by a special process. They offer high mechanical strength and are not affected by shocks and knocks.

see also... Page
GN 227.7 Handwheels QVX

How to order		¹ Material
²	d	
³	s ₀	
⁴	Finish	

GN 227.6-ST-60-V7-SW

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

