



1

d ₁	d ₂	d ₃	h ±0,5	For thread up to max.	Static load in kN	
					Steel	Stainless Steel
25 ±0,2	8,5	15	8	M 8	40	27,1
32 ±0,3	13	20	10	M 10	65	43,4
45 +0,3/-0,5	20	30	12,5	M 16	120	84
58 +0,3/-1	29	38	16	M 24	210	148
70 +0,3/-1	36	48	20	M 30	330	225
80 +0,3/-1,2	44	61	20	M 36	495	323
105 +0,3/-1,6	58	78	25	M 48	920	546

Specification

Steel 1.7225 (42 CrMo 4 V)
Zinc plated, blue passivated

2

ST

Stainless steel AISI 303

NI

RoHS

Spherical leveling washers GN 350.3 have been designed to match the leveling sets GN 350, GN 350.1, GN 350.2 and GN 350.5.

The two spherical washers are used together „unddetachably“.

The load bearing capacity of these spherical washers is relatively high. This is not only due to the material quality but also to the matched sphere of the concave „pan“.

Furthermore it is recommended using high-strength washers for bridging d₂.

see also...

	Page
GN 350 Leveling Sets (Long Version)	QVX
GN 350.1 Leveling Sets (Short Version)	QVX
GN 350.2 Leveling Sets (with Spherical Washer, without Locknut)	QVX
GN 350.5 Leveling Sets (with Spherical Washer, with Locknut)	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order

GN 350.3-80-ST

1 d₁

2 Material