



ROSTFREI®
Inox
Stainless
Steel

4 Type

EE with 2 female threads

ES with female thread / threaded stud

SS with 2 threaded studs

1 **2**

d ₁	h												d ₂	Length l	s	t
	Type EE				Type ES				Type SS							
8	8	13	-	8	13	-	-	8	13	-	-	M 3	3	6	1	3
10	10	15	20	10	15	20	-	10	15	20	-	M 4	10	10	1,2	4
15	10	15	20	10	15	20	25	10	15	20	25	M 4	10	10	1,4	4
20	15	20	25	15	20	25	30	15	20	25	30	M 6	18	18	2	6
25	20	25	30	15	20	30	-	15	20	30	-	M 6	18	18	2	6
30	20	30	40	15	30	40	-	15	30	40	-	M 8	20	20	2	8
40	20	30	40	20	30	40	-	20	30	40	-	M 8	23	23	2	8
50	30	40	50	20	30	40	50	20	30	40	50	M 10	28	28	2	10
60	30	40	50	30	40	50	-	30	40	50	-	M 10	28	28	2	10
70	30	45	-	30	45	-	-	30	45	-	-	M 10	27	27	3	10
75	30	40	55	25	40	55	-	25	40	55	-	M 12	37	37	3	12
100	40	55	75	40	55	75	-	40	55	75	-	M 16	41	41	3	16
125	55	75	-	55	75	-	-	55	75	-	-	M 16	41	41	3	16

Specification

- Natural rubber (NR)
 - black
 - vulcanized to the cover plates
 - temperature resistant up to 80 °C

GN 351

Cover plates, threaded bushings / studs
Steel, zinc plated, blue passivated

Rubber hardness Shore A ±5

- soft **40**
- medium **55**
- hard **70**

GN 451

Cover plates, threaded bushings / studs
Stainless Steel AISI 304

Rubber hardness Shore A ±5

- soft* **40**
- medium **55**
- hard* **70**

• *Elastomer characteristics* → Page 1483

• *Stainless Steel characteristics* → Page 1489

• RoHS

5

Information

* not available from stock, requires a minimum order quantity

Rubber buffers GN 351 / GN 451 are suitable for the elastic mounting of machine units such as motors, compressors and pumps.

see also...

- *Resilient characteristics* → Page 1465 ff.
- *Buffers GN 353 / GN 453* → Page 1082 / 1083

On request

- Rubber in gray

How to order (Steel)	1 d ₁
	2 h
	3 d ₂
GN 351-30-30-M8-EE-55	4 Type
	5 Hardness

How to order (Stainless Steel)	1 d ₁
	2 h
	3 d ₂
GN 451-100-40-M16-ES-55	4 Type
	5 Hardness