



2 Bore code
B Without keyway
K With keyway DIN 6885-1 P9

1 d₁	3 d₂ H7 Bore			b	d₃	l₁	l₂ ≈
80	10	12	-	14	26	16	29
100	10	12	-	15	28	17	33
125	12	14	-	16	31	18	36
160	14	16	-	18	36	20	40
200	18	20	22	22	42	24	45
250	22	24	26	26	48	28	50
315	26	28	30	28	56	33	56
400	30	32	-	32	65	38	63

Specification

- Aluminum**
- Hub machined
 - Rim
 - turned and polished
 - Radial and axial runout of the rim < 0.4
 - Unmachined body shot-blasted

RoHS

Disk handwheels DIN 3670 have recessed grips at their back. As a rule they are supplied without handle, but the mounting of a handle is possible. The handwheel diameter d₁=80 and d₁=400 are not provided in the official standard sheet.

Technical Information	Page
Keyways P9 DIN 6885-1	QVX
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Accessory	
GN 184 Countersunk Washers (for Axial Fastening)	QVX

How to order	1 d ₁
DIN 3670-125-K12	2 Bore code
	3 d ₂