



4 Form

- A 2x2 bores for countersunk screws
- C 2x2 threaded studs

2

3

l ₁		l ₂	d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ +0,5	l ₃		l ₄		l ₅	m ₁	m ₂	m ₃	m ₄
elongated on one side	elongated on both sides									ZD	NI	ZD	NI					
63	-	50	M 6	6,3	6	11,5	6	6,5	13	18,5	21	31,5	34	12	43	30	15	28
-	76	50	M 6	6,3	6	11,5	6	6,5	13	31,5	34	31,5	34	12	56	30	28	28
90	-	60	M 8	8,4	8	15	8	8,5	17	21,5	26	51,5	56	14	63	36	18	45
-	120	60	M 8	8,4	8	15	8	8,5	17	51,5	56	51,5	56	14	90	36	45	45

Specification

1

5

- Zinc die casting **ZD**
plastic coated
black, RAL 9005, textured finish
silver, RAL 9006, textured finish **● SW**
● SR
- Stainless Steel (only type A) **NI**
- AISI CF-8
- matte shot blasted **GS**
- Pin
- Stainless Steel AISI 303 (A2)
for ZD
- Stainless Steel AISI 316Ti (A4)
for NI
- Threaded stud (type C)
Stainless Steel AISI 316
- *Stainless Steel characteristics* → Page 1489
- *Load rating information* → Page 1460
- RoHS

Information

Hinges GN 237 with horizontally elongated hinge wings are made in a compact and sturdy design. They are used when larger spacings are required for the attachment bore holes.

see also

- *List of hinge types* → Page 956 ff.
- *Stainless Steel-Plates with tapped holes GN 2372* → Page 960
- *Stainless Steel-Spacer plates GN 2370* → Page 961

How to order

1	Material
2	l ₁
3	l ₂
4	Type
5	Finish

GN 237-ZD-76-50-A-SR

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

