


x = ground

Application example



3 Type

- B** Smooth contact face
- K** Spherical contact face
- R** Serrated contact face

1

2

h Type B: ±0,01 Type K / R: ±0,1	d₁	d₂ Type B / R	t min.	A/F	e Width across corners
15	M 8	17	6	17	19,4
20	M 10	19	10	19	21,9
20	M 12	22	10	22	25,2
25	M 8	17	12	17	19,4
25	M 12	22	15	22	25,2
30	M 10	19	15	19	21,9
30	M 12	22	18	22	25,2
30	M 16	30	20	30	33
40	M 10	19	15	19	21,9
40	M 12	22	18	22	25,2
50	M 12	22	18	22	25,2
50	M 16	30	24	30	33

Specification

- Steel
 - Hardened
 - Blackened
- RoHS

Information

Positioning elements GN 409.2 with internal thread are designed for use as locating plungers, stops and thrust blocks.

How to order

GN 409.2-25-M8-R

1	h
2	d₁
3	Type