



EDELSTAHL®
Rost
frei
Inox
Stainless
Steel

Length l	² d ₁ H9 Bore	² s H11 Square	d ₂	h ₁	h ₂ ≈	h ₃	h ₄ ≈	Ø Handle
80	B 10	V 10	22	22	15,4	6,6	45	18
100	B 12	V 12	26	26	17,7	8,3	55	21
125	B 14	V 14	28	28	18,8	9,2	71	23
160	B 17	V 17	32	32	22,6	9,4	71	23
200	B 19	V19	38	38	28	9,4	71	23

Specification

- Body
Stainless Steel precision casting
AISI CF-8
Face of the hub machined
- Revolving handles
similar to GN 598.1
 - Plastic (Duroplast PF)
black, shiny finish
 - Spindle
Stainless Steel AISI 304
- Square DIN 79 → Page 1424
- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- Plastic characteristics → Page 1483
- RoHS

On request

- Stainless Steel-Cranked handles
with retractable handle GN 798.5

Information

Stainless Steel-Cranked handles GN 269 have been designed to comply with stringent hygiene requirements.

The cylindrical handles are made of duroplast which in general provides good stability when exposed to chemicals.

How to order

GN 269-100-V12

1 Length l

2 s (d.)