


ROSTFREI  
Inox  
Stainless  
Steel



Length $l \pm 0,25$	$h_1$	$h_2$	$h_3$	$F_1$ Static load in N folded out
100	34	44,5	55	500
120	34	44,5	55	500
180	34	44,5	55	500

**Specification**

- Handle
  - Steel, chrome-plated
  - Stainless Steel AISI 303 matte shot-blasted



- Attachment part
  - Plastic
  - Technopolymer (Polyamide PA)
  - temperature resistant up to 100 °C
  - black, matte

- Cover
  - Plastic
  - Technopolymer (Polyamide PA)
  - temperature resistant up to 100 °C
  - black-gray, matte

- Load rating information → Page 1453
- Plastic characteristics → Page 1483
- Stainless Steel characteristics → Page 1489

• RoHS

**Information**

Folding handles GN 425.5 are used in places where the handle must not protrude or protrude only a short distance.

The handle is locked in place in the resting position by means of a spring-loaded (spring disks) thrust bolt.

The static load capacity value given in the table is an approximate value which, if exceeded, may result in permanent deformation or fracture of the plastic attachment part. The folding handle GN 425.2 may be used as an alternative.

see also...

- Folding handles with recessed tray GN 425.8 (with handle locking or spring-loaded return) → Page 124
- Folding handles GN 825.1 (Plastic, with spring-loaded return) → Page 128

How to order

**GN 425.5-100-NI**

1 Length l

2 Material

