


2 Identification no.

2 with 2 Stainless Steel-Clamping screws DIN 912



1

d ₁ Bore B	b Swivel width	d ₂	d ₃ Clamping thread	k	l ₁	l ₂	m ₁	m ₂	t	x ₁	x ₂	y	Clamping kit for d ₃
B 12	25	5,5	M 6	25	72,5	34,5	24	48,5	7	50	38	35	GN 911-M6-22
B 14	25	5,5	M 6	25	72,5	34,5	24	48,5	7	50	38	35	GN 911-M6-22
B 16	25	5,5	M 6	25	72,5	34,5	24	48,5	7	50	38	35	GN 911-M6-22
B 18	25	5,5	M 6	25	72,5	34,5	24	48,5	7	50	38	35	GN 911-M6-22

Specification

- Aluminum
 - plastic coated black, RAL 9005, textured finish **● SW**
 - blank **○ BL**
 - matte shot-blasted
- Clamping bore mechanically machined
- Socket cap screws DIN 912 Stainless Steel AISI 304
- Hexagon nuts DIN 985 Stainless Steel AISI 304
- Stainless Steel characteristics → Page 1489
- RoHS

Accessory

- Clamping kits GN 911 → Page 1242

3

Information

GN 281 swivel clamp connector joints are an assembly of the swivel clamp connectors GN 271 and GN 275.

The clamping bore is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462 respectively.

The standard version of the clamping screws are socket cap screws with hexagonal socket DIN 912. They can be replaced by clamping kits GN 911 (see table of dimensions).

see also...

- Construction tubes GN 990 → Page 1277
- Retaining rods / Retaining tubes GN 480.1 → Page 1276
- Swivel clamp connector bases GN 271 → Page 1220
- Swivel clamp connectors GN 275 → Page 1224

How to order

GN281-B14-2-BL

1	d ₁
2	Identification no.
3	Finish