



1		2		3													
l <sub>1</sub>	d <sub>1</sub>			l <sub>2</sub>						d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	Stroke	
22	M 3	-	-	6	8	10	12	16	-	-	8	10,5	18,5	2	23	3	
22	M 4	M 5	-	12	16	20	25	32	-	-	8	10,5	18,5	2	23	3	
30	M 3	-	-	6	8	10	12	16	-	-	10	13	24,5	4	31	3,5	
30	M 4	-	-	12	16	20	25	32	-	-	10	13	24,5	4	31	3,5	
30	M 5	M 6	-	12	16	20	25	32	40	50	10	13	24,5	4	31	3,5	
45	M 4	-	-	12	16	20	25	32	-	-	10	13	24,5	4	34	3,5	
45	M 5	M 6	-	12	16	20	25	32	40	50	10	13	24,5	4	34	3,5	
63	M 6	M 8	-	16	20	25	32	40	50	63	13,5	17,5	31	6,5	45	4	
78	M 8	M 10	M 12	20	25	32	40	50	63	80	16	21	36	8	54	4	
92	M 10	M 12	-	20	25	32	40	50	63	80	19	24	43	11	64	4	
108	M 12	M 16	-	32	40	50	63	80	-	-	23	30	50,5	12	75	5	

**Specification**

- Handle  
Zinc die casting
- Powder coated  
Black, RAL 9005, textured finish **● SW**  
Black, RAL 9005, silk finish **● SZ**  
Orange, RAL 2004, textured finish **● OS**  
Red, RAL 3000, textured finish **● RS**  
Silver, RAL 9006, textured finish **● SR**
- Chrome plated **● CR**
- Uncoated **● RH**  
Tumbled
- Threaded stud and retaining screw  
Stainless steel AISI 303
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**On request**

- With inch threads

**Information**

Adjustable hand levers GN 300.1 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- *Adjustable Hand Levers GN 300 (Threaded Stud Steel)* → Page 429
- *Adjustable Hand Levers GN 300.5 (Stainless Steel, Matte Shot-Blasted)* → Page 441
- *Adjustable Hand Levers GN 300.6 (Stainless Steel, Polished)* → Page 441
- *Adjustable Hand Levers GN 303.1 (with Push Button)* → Page 447

**How to order**

1	l <sub>1</sub>
2	d <sub>1</sub>
3	l <sub>2</sub>
4	Color (Finish)

**GN 300.1-63-M8-32- RS**