



- 3 Type**
- A** Mounting from the back with thread
 - B** Mounting from the operator's side with through hole
 - C** Mounting from the operator's side by welding
- 4 Identification no.**
- 1** Handle 90° foldaway
 - 2** Handle 90° foldaway, with retaining springs
 - 3** Handle 180° foldaway
 - 4** Handle 180° foldaway, with retaining springs

Length l	b ₁	b ₂	b ₃	d ₁	d ₂	h ₁	h ₂ ≈	h ₃	h ₄	m	t ₁	t ₂
120	124	20	106	M 6	6,4	16	53	49	59	60	10	9,6

Specification

- Attachment part
Stainless steel precision casting AISI CF-8 **NI**
- Matte shot-blasted **GS**
- Powder coated Black, RAL 9005, textured finish **● SW** (only type A and B)
- Handle
Stainless steel AISI 304
Matte shot-blasted
- Retaining springs
Spring steel AISI 301
- Load Rating Information → Page 2106
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Stainless steel folding handles GN 425.9 are used where the handle must only protrude a short distance in the resting position.

Folding handles numbers 1 and 2 are suitable for side “access”, as these have a 90° limit stop. If used from above, numbers 3 and 4 with a handle which can fold freely through 180° are a better version.

The retaining springs of numbers 2 and 4 keep the handle in any position. This keeps the handle in a position which can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

see also...

- Folding Handles with Recessed Tray GN 425.8
(Steel / Stainless Steel, with Handle Locking or Spring-Loaded Return)
→ Page 176

How to order	1 Length l
	2 Material
	3 Type
	4 Identification no.
	5 Finish
GN 425.9-120-NI-A-1-SW	