



ROSTFREI
Inox
Stainless
Steel

3 Type

- A** Thread for fixing from the back
- B** Through-hole for fixing from the operators side
- C** Fixed from the operators side by means of welding

4 Identification no.

- 1** Handle 90° foldaway
- 2** Handle 90° foldaway, with retaining spring
- 3** Handle 180° foldaway
- 4** Handle 180° foldaway, with retaining spring

1

Length l	b ₁	b ₂	b ₃	d ₁	d ₂	h ₁	h ₂ ≈	h ₃	h ₄	m	t ₁	t ₂
120	124	20	106	M 6	6,4	16	53	49	59	60	10	9,6

Specification

2

5

- Attachment part
Stainless Steel precision casting
AISI CF-8 **NI**
- matte shot-blasted **GS**
- plastic coated
(only type A and B)
black, RAL 9005, textured finish **● SW**
- Handle
Stainless Steel
AISI 304
matte shot-blasted
- Retaining springs
spring steel
AISI 301
- Load rating information → Page XYZ
- Stainless Steel characteristics → Page 1489
- RoHS

Information

GN 425.9 Stainless Steel-Folding handles are used where the handle must only protrude a short distance in the resting position.

Folding handles numbers 1 and 2 are suitable for side “access,” as these have a 90° limit stop. If used from above, numbers 3 and 4 with a handle which can fold freely through 180° are a better version.

The retaining springs of numbers 2 and 4 keep the handle in any position. This keeps the handle in a position which can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

see also...

- Folding handles GN 425.8 (with recessed tray) → Page 124

How to order

1	Length l
2	Material
3	Type
4	Identification no.
5	Finish

GN 425.9-120-NI-A-1-SW