



1

2

l_1	d_1	d_3	d_4	h_1	h_3	h_4 Stroke	t min.
63	M 6	24	17,5	34,5	48,5	4	12,5
78	M 8	25	21	39,5	58,5	4	14
92	M 10	30	24	46,5	68,5	4	18
108	M 12	35	30	56,5	82	5	26,5

Specification

3

- Handle
Zinc die casting
- Plastic coated
black, RAL 9005, textured finish ● **SW**
black, RAL 9011, silk finish ● **SZ**
orange, RAL 2004, textured finish ● **OS**
red, RAL 3000, textured finish ● **RS**
silver, RAL 9006, textured finish ● **SR**
- chrome-plated ● **CR**
- Bushing
Steel
nitrided, blackened
- Retaining screw
Steel, blackened
- RoHS

Information

Adjustable hand levers GN 300.4 are produced with a clamping area which is linked via a thrust ball bearing (axial bearing) to the threaded bushing of the hand lever. This has led to the following advantages:

- **Doubled** clamping force through vastly reduced friction.
- There is no movement on the contact area between adjustable hand lever and component which greatly reduces any marking on the clamping area.
- In addition a reduced creep factor has been achieved by the increased preload.

How to order

GN 300.4-78-M8-SW

1	l_1
2	d_1
3	Color (Finish)