



4 Type (Base plate)

A0 Without rubber pad

A1 With rubber pad, clipped on, black

A3 With rubber pad, vulcanized, black

d ₁	d ₂	1					2					l ₇	d ₃	h ₁	h ₆	l ₈	m	r	s		
		3					3														
		Version S / SK					Version U / UK					Vers. X									
50	M 8	40	50	63	-	-	-	-	-	-	-	25	13	2,5	4	60	45	15	2		
50	M 10	50	60	80	100	-	-	-	-	-	28	13	2,5	4	60	45	15	2			
50	M 12	60	80	100	125	-	-	-	-	-	32	13	2,5	4	60	45	15	2			
50	M 16	-	-	-	-	75	100	125	150	200	250	37	13	2,5	4	60	45	15	2		
60	M 8	40	50	63	-	-	-	-	-	-	25	13	2,5	4,5	65	50	15	2			
60	M 10	50	60	80	100	-	-	-	-	-	28	13	2,5	4,5	65	50	15	2			
60	M 12	60	80	100	125	-	-	-	-	-	32	13	2,5	4,5	65	50	15	2			
60	M 16	-	-	-	-	75	100	125	150	200	250	37	13	2,5	4,5	65	50	15	2		
80	M 8	40	50	63	-	-	-	-	-	-	26	13	3	5	85	70	15	2			
80	M 10	50	60	80	100	-	-	-	-	-	29	13	3	5	85	70	15	2			
80	M 12	60	80	100	125	-	-	-	-	-	32	13	3	5	85	70	15	2			
80	M 16	-	-	-	-	75	100	125	150	200	250	38	13	3	5	85	70	15	2		
80	M 20	-	-	-	-	75	100	125	150	200	250	45	13	3	5	85	70	15	2		
80	M 24	-	-	-	-	100	125	150	200	300	-	13	3	5	85	70	15	2			

Versions of threaded stem

<p>S Without nut SK With nut</p>	<p>U Without nut UK With nut</p>	<p>X With internal thread</p>
<p>External hex at the bottom at d_2 M 8, M 10, M 12</p>	<p>Hex socket at the top and wrench flat at the bottom at d_2 M 16, M 20, M 24</p>	<p>External hex with internal thread at d_2 M 8, M 10, M 12, M 16, M 20</p>

d_1	d_2	h_3	h_4	A/F ₁	A/F ₂	A/F ₃	A/F ₇	t
50	M 8	11	-	17	-	-	14	8
50	M 10	11	-	17	-	-	14	10
50	M 12	11	-	17	-	-	17	12
50	M 16	-	17	-	12	8	22	16
60	M 8	11	-	17	-	-	14	8
60	M 10	11	-	17	-	-	14	10
60	M 12	11	-	17	-	-	17	12
60	M 16	-	17	-	12	8	22	16
80	M 8	12	-	17	-	-	14	8
80	M 10	12	-	17	-	-	14	10
80	M 12	12	-	17	-	-	17	12
80	M 16	-	18	-	12	8	22	16
80	M 20	-	19	-	15	10	27	20
80	M 24	-	22	-	19	12	-	-

Specification

- Base plate
Steel
Zinc plated, blue passivated
- Threaded stem
Steel
Zinc plated, blue passivated
- Hex nut ISO 4032
Steel
Zinc plated, blue passivated
- Rubber pad
- Clipped on
- Black, TPE (Santoprene®)
≈ 80 Shore A
- Rubber pad
- Vulcanized
- Black, NBR (Perbunan®)
70±5 Shore A
- Load Rating Information → Page 2144
- Elastomer Characteristics → Page 2158
- RoHS

Information

Leveling feet GN 42 can be used in a host of combinations of base plates and adjustable spindle versions.

The leveling feet can be screwed to the mounting surface using the fixing lug, which prevents lateral shifting. Moreover, the types with the rubber pad protect sensitive surfaces.

The leveling feet are supplied fully assembled and are not removable.

see also...

- Leveling Feet GN 40 (Steel, without Fixing Lug) → Page 1460
- Leveling Feet GN 42 (Steel, with Fixing Lug, Rect. Shape) → Page 1468
- Leveling Feet GN 43 (Stainless Steel, with Fixing Lug) → Page 1470
- Leveling Feet GN 44 / GN 45 (Stainless Steel, without / with Fixing Lug) → Page 1464 / 1474
- Insert Bushings GN 448 (Plastic, for Tubes) → Page 1498 / 1499
- Insert Bushings GN 992 / GN 992.5 (Aluminum / Stainless Steel, for Tubes) → Page 1501

How to order

GN 42-50-M12-32-D3-X

1	d_1
2	d_2
3	l_7 (l ₁)
4	Type (Base plate)
5	Version (Stem)

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

