



4 Type

- A** Without nut, without rubber pad
- B** With nut, without rubber pad
- AG** Without nut, with rubber pad
- BG** With nut, with rubber pad

1 2 3

d ₁	d ₂	l ₁		b	d ₃	k ₁	k ₂	l ₂	l ₃	l ₄	A/F	Ball Ø	Static load in kN (see information)		
60	M 8	43	68	-	96,5	8,5	50	18	30	14	21	14	14	14	
60	M 10	43	68	98	96,5	8,5	50	18	30	14	21	14	14	14	
60	M 12	43	68	98	96,5	8,5	50	18	30	14	21	14	14	14	
60	M 14	68	98	148	96,5	8,5	50	18	30	14	21	14	14	14	
60	M 16	68	108	148	168	96,5	8,5	50	18	30	14	21	16	14	14
80	M 8	43	68	-	130	10,5	70	25	31	14	22	14	14	14	
80	M 10	43	68	98	130	10,5	70	25	31	14	22	14	14	16	
80	M 12	43	68	98	130	10,5	70	25	31	14	22	14	14	16	
80	M 14	68	98	148	130	10,5	70	25	31	14	22	14	14	16	
80	M 16	68	108	148	168	130	10,5	70	25	31	14	22	16	14	16



Specification

- Foot
Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Black, matte finish
 - Temperature resistant up to 100 °C
- Rubber pad (NBR)
70 Shore A, black
- **GN 445**
 - Threaded stud steel
Property class 5.8
Zinc plated, blue passivated
 - Hex nut ISO 4032
Steel zinc plated, blue passivated
- **GN 445.5**
 - Threaded stud
Stainless steel AISI 303
 - Hex nut ISO 4032
Stainless steel AISI 304
- *Strength Values* → Page 2152
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Leveling feet GN 445 / GN 445.5 are capable of withstanding high static loads through the use of a high density plastic material coupled with a design which distributes the load over a larger area.

The values given in the table regarding the static load capacity serve as a guide line only and if these are exceeded serious permanent deformation or breakage of the plastic socket could occur.

The above values have been arrived at by a series of tests whereby a limited number of leveling feet were subjected for a limited time to a vertical static load to the feet.

The fixing holes are closed by a thin plastic layer, which may be easily punctured.

Leveling feet GN 445 / GN 445.5 are supplied assembled, but are removable.

How to order (Threaded stud steel)

1 2 3 4
GN 445-80-M10-98-B

1	d ₁
2	d ₂
3	l ₁
4	Type

How to order (Threaded stud stainless steel)

1 2 3 4
GN 445.5-60-M16-168-A

1	d ₁
2	d ₂
3	l ₁
4	Type

