



1	2	3									d₂	d₃	h₁	h₂	h₃	h₄	
l₁	d₁																Stroke
30	M 4	-	12	16	20	25	32	-	-	10	13	26,5	4	31	3,5		
30	M 5	M 6	12	16	20	25	32	40	50	10	13	26,5	4	31	3,5		
45	M 4	-	12	16	20	25	32	-	-	10	13	26,5	4	35	3,5		
45	M 5	M 6	12	16	20	25	32	40	50	10	13	26,5	4	35	3,5		
63	M 6	M 8	16	20	25	32	40	50	63	13,5	17,5	32,5	6,5	45	4		
78	M 8	M 10	20	25	32	40	50	63	80	16	21	37,5	8	55	4		

Specification

- Handle
Zinc die casting
- Plastic coated
black, RAL 9005
textured finish **● SW**
- Releasing button
Plastic
black, RAL 9005 **● S**
orange, RAL 2004 **● O**
gray, RAL 7035 **● G**
- Threaded stud
Steel
zinc plated, blue passivated
- RoHS

On request

- Handle in colors of GN 300

Information

Adjustable hand levers GN 303.2 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

The releasing button is a design element that offers an easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.

see also...

- *Adjustable hand levers GN 303.1 (with push button, threaded stud Stainless Steel) → Page 331*

How to order

1	l₁
2	d₁
3	l₂
4	Color handle
5	Color releasing button

GN 303.2-63-M8-25-SW-G