



1

2

l_1	d_1	d_2	d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
63	M 6	14	14,8	19	43,8	16,3	60,1	2,5	10
63	M 8	18	18,8	19	45,8	18,3	62,1	2,5	12
78	M 8	18	18,8	24	49,3	16,5	69,3	3	12
78	M 10	22	22,8	24	51,3	18,5	71,3	3	15

Specification

- Handle
Stainless Steel precision casting
- AISI CF-8
- polished ($R_a < 0.8 \mu\text{m}$) **PL**
- Threaded bushing
Stainless Steel AISI 304
- Sealing ring / Wiper
hydrogenated acrylonitrile butadiene rubber (H-NBR)
- blue
- temperature resistant -25°C to $+150^\circ\text{C}$
- Hardness 85 ± 5 Shore A
- FDA compliant
- *Elastomer characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

3

Information

Adjustable hand levers GN 305 with solid Stainless Steel-Handle are intended for use in hygiene areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the impervious exterior surfaces prevent adherence of dirt and facilitate cleaning.

Adjustable hand levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position.

The threaded insert is moveably attached to the handle with serrations. When pulling the handle, the serration frees itself and can be re-located into any required position. Engagement is achieved by releasing the lever.

see also...

- *Product family Hygienic Design* → Page 18
- *Sealing rings Hygienic Design GN 7600* → Page 881
- *Stainless Steel-Star knobs Hygienic Design GN 5435* → Page 419
- *Stainless Steel-Three knob handles Hygienic Design GN 5445*
→ Page 429

How to order

GN 305-63-M8-PL

1

 l_1

2

 d_1

3

Finish