



¹ d ₁	² Length l								d ₂	d ₃	h	k
M 2	4	6	8	10	-	-	-	-	9	4,5	5,3	2
M 2,5	4	6	8	10	12	-	-	-	11	5	6,5	2,5
M 3	6	8	10	12	16	20	-	-	12	6	7,5	2,5
M 4	5	8	10	12	16	20	25	-	16	8	9,5	3,5
M 5	6	8	10	12	16	20	25	30	20	10	11,5	4
M 6	8	10	12	16	20	25	30	35	24	12	15	5
M 8	12	16	20	25	30	35	40	-	30	16	18	6
M 10	12	15	20	25	30	35	40	-	36	20	23	8

Specification

- Steel
 - Tensile strength class 5
 - visible face fine turned
 - blackened
 - zinc plated, blue passivated
 - Stainless Steel
 - AISI 303
 - matte shot-blasted
- **ZB**
NI
- *Stainless Steel characteristics* → Page 1489
 - *Strength values of screws* → Page 1481
 - **RoHS**

Information

Knurled screws DIN 464 are machined from solid bar. Unlike in the official standard sheet, they are generally made with thread right up to the head and without recess groove at the end of the thread. The official standard sheet also provides for the sizes M1 / M1,2 and M1,6.

see also...

- *Flat knurled screws DIN 653* → Page 459
- *Knurled screws GN 653.2 (with recessed stud for loss protection)* → Page 461
- *Stainless Steel-Knurled screws GN 535* → Page 452
- *Knurled screws DIN 464 with loss protection GN 111.7* → Page 1426

How to order (Steel, blackened)	1	d ₁
¹ ² DIN 464-M6-20	2	Length l

How to order (Steel, zinc plated)	1	d ₁
¹ ² ³ DIN 464-M2,5-6-ZB	2	Length l
	3	Finish

How to order (Stainless Steel)	1	d ₁
¹ ² ³ DIN 464-M10-35-NI	2	Length l
	3	Material

