



GN 307 Adjustable hand levers

Zinc die casting, with threaded stud steel and washer



Application example



1	2	3						d ₂	d ₃	d ₄	l ₃	h ₁	h ₂	h ₃	h ₄ Stroke	s
30	M 5	12	16	20	25	32	13	10	13	0,4	24,5	4	31	3,5	2,5	
45	M 6	16	20	25	32	40	15	10	15	0,4	24,5	4	34	3,5	3	
63	M 8	20	25	32	40	50	20	13,5	17,5	0,4	31	6,5	45	4	3,5	
78	M 10	20	25	32	40	50	25	16	21	0,5	36	12	54	4	4	

Specification

- Handle
Zinc die casting
- Plastic coated
black, RAL 9005, textured finish ● **SW**
orange, RAL 2004, textured finish ● **OS**
red, RAL 3000, textured finish ● **RS**
silver, RAL 9006, textured finish ● **SR**
- Threaded stud and retaining screw
Steel
- Tensile strength class 5.8
- blackened
- Washer
Steel
- case hardened
- blackened
- Strength values of screws → Page 1481
- RoHS



Information

Adjustable hand levers GN 307 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. On releasing the handle the serrations re-engage automatically.

When pulling the handle, the serration frees itself and can be re-located into any required position. Engagement is achieved by „releasing“ the lever.

The washer cannot be removed and does not turn when the lever is actuated. It protects the clamped surface from damage. One typical application is to use the hand lever for slotted holes.

see also...

- Adjustable hand levers GN 300 (without washer) → Page 319
- Adjustable hand levers GN 300.4 (with increased clamping force) → Page 333
- Adjustable hand levers GN 303 (with push button) → Page 329

How to order

1 2 3 4
GN 307-45-M6-25-SW

- 1 l₁
- 2 d₁
- 3 l₂
- 4 Color

