


Clamping thread d_3 

Clamping kit GN 511

¹ d_1 Bore for shaft tol. h11	² d_2 Bore for shaft tol. h11	d_3 Clamping thread	k	l_1	l_2	m	S_1 Square	S_2 Square	Clamping kits for d_3 
B 8	B 8	M 4	14	38	7	24	-	-	GN 511-M4-14
B 10	B 8	M 5	16	44	8	28	8	-	GN 511-M5-16
B 10	B 10	M 5	16	44	8	28	8	8	GN 511-M5-16
B 12	B 8	M 5	16	45	8	29	10	-	GN 511-M5-16
B 12	B 10	M 5	16	45	8	29	10	10	GN 511-M5-16
B 12	B 12	M 5	16	45	8	29	10	10	GN 511-M5-16
B 15	B 10	M 6	20	55	10	35	12	8	GN 511-M6-20
B 15	B 12	M 6	20	55	10	35	12	10	GN 511-M6-20
B 15	B 15	M 6	20	55	10	35	12	12	GN 511-M6-20
B 16	B 10	M 6	20	55	10	35	-	8	GN 511-M6-20
B 16	B 12	M 6	20	55	10	35	-	10	GN 511-M6-20
B 16	B 15	M 6	20	55	10	35	-	12	GN 511-M6-20
B 16	B 16	M 6	20	55	10	35	-	-	GN 511-M6-20
B 20	B 12	M 6	25	66	12,5	41	16	12	GN 511-M6-25
B 20	B 15	M 6	25	66	12,5	41	16	12	GN 511-M6-25
B 20	B 16	M 6	25	66	12,5	41	16	-	GN 511-M6-25
B 20	B 20	M 6	25	66	12,5	41	16	16	GN 511-M6-25

Specification**Mounting clamp**

Aluminum

- Matte finish, tumbled
- Anodized, black

MT
ELS**Socket cap screws ISO 4762**

Stainless steel

RoHS

Technical Information**Page**

Range of Mountings Clamps	QVX
Application Examples Mountings Clamps	QVX
ISO Fundamental Tolerances	QVX

Accessory

GN 511 Clamping Kits	QVX
GN 480.1 Retaining Rods / Retaining Tubes	QVX

In the standard version, the clamping screw is a socket cap screw with hexagonal socket ISO 4762. It can be replaced by a clamping kit GN 511 (article code see table of dimensions).

see also...

GN 174 Two-Way Mounting Clamps	QVX
GN 490 Swivel Clamp Connector Joints	QVX
GN 131 Two-Way Connector Clamps	QVX

How to order

¹	d_1
²	d_2
³	Finish

GN 474.1-B12-B12-ELS