



**3** Type  
**A** With bore  
**W** With bolt

<b>1</b> $d_1$ Bore for shaft tol. h11	<b>2</b> $d_2$ Type A	<b>2</b> $d_3$ Type W	$d_4$ Clamping thread	$d_5$	$k$	$l_1$	$l_2$	$l_3$	$l_4$	$s$ Square	$t$	Clamping kits for $d_4$ 
B 8	B 8	8	M 4	M 4	16	16	13	26	5,5	-	8	GN 511-M4-16
B 10	B 10	10	M 5	M 5	20	17	15,5	31,5	7	8	10	GN 511-M5-20
B 12	B 12	12	M 5	M 5	20	19	16,5	35,5	8	10	12	GN 511-M5-20
B 15	B 15	15	M 6	M 6	25	21	20	43,5	10	12	15	GN 511-M6-25
B 16	B 16	16	M 6	M 6	25	24	20	45	11	-	16	GN 511-M6-25
B 20	B 20	20	M 6	M 6	30	26	22	51	12	16	18	GN 511-M6-30

**Specification**

- Aluminum
  - Matte finish, tumbled **MT**
  - Black anodized **ELS**
- Bolt (Type W)  
Stainless steel AISI 303
- Socket cap screw DIN 912  
Stainless steel AISI 304
- Grub screw DIN 913 (Type A)  
Stainless steel AISI 304
- Grub screw DIN 915 (Type W)  
Stainless steel AISI 304
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

**Accessory**

- Clamping Kits GN 511 → Page 1804

**Information**

The T-mounting clamps GN 476 (Type W) are an alternative to twistable two-way mounting clamps GN 475 if high angular forces are required. In the standard version, the clamping screw at the clamping thread  $d_4$  is a socket cap screw with hexagonal socket DIN 912. It can be replaced by a clamping kit GN 511 (article code see table of dimensions).

see also...

- Retaining Rods / Retaining Tubes GN 480.1 → Page 1833

How to order (With bore)

<b>1</b>	$d_1$
<b>2</b>	$d_2$
<b>3</b>	Type
<b>4</b>	Finish

**GN 476-B12-B12-A-MT**

How to order (With bolt)

<b>1</b>	$d_1$
<b>2</b>	$d_3$
<b>3</b>	Type
<b>4</b>	Finish

**GN 476-B12-12-W-ELS**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9