



4 Type (Base plate)

- B1** Matte shot-blasted, rubber inlaid, black
- B2** Matte shot-blasted, rubber inlaid, white
- B3*** Matte shot-blasted, rubber vulcanised, black
- B4*** Matte shot-blasted, rubber vulcanised, white
- C3*** Polished, rubber vulcanised, black
- C4*** Polished, rubber vulcanised, white

d ₁	d ₂	1										3				3				3				A/F ₇	t
		Version S / SK		Version T / TK and U / UK								Version V / VK				Version W				Vers. X					
50	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	37	14	8		
50	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	40	14	10		
50	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	43	17	12		
50	M 16	-	-	-	-	75	100	125	150	200	250	-	-	-	-	-	-	-	-	-	49	22	16		
60	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	38	14	8		
60	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	41	14	10		
60	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	45	17	12		
60	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	123	148	173	198	50	22	16			
80	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	40	14	8		
80	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	43	14	10		
80	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	47	17	12		
80	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	125	150	175	200	52	22	16			
80	M 20	-	-	-	-	75	100	125	150	200	250	100	125	150	200	149	174	199	249	60	27	20			
80	M 24	-	-	-	-	100	125	150	200	300	-	100	150	200	-	174	224	274	-	-	-	-	-		
100	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	42	14	8		
100	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	45	14	10		
100	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	49	17	12		
100	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	126	151	176	201	54	22	16			
100	M 20	-	-	-	-	75	100	125	150	200	250	100	125	150	200	151	176	201	251	62	27	20			
100	M 24	-	-	-	-	100	125	150	200	300	-	100	150	200	-	176	226	276	-	-	-	-	-		
120	M 20	-	-	-	-	100	125	150	200	250	-	-	-	-	-	-	-	-	-	-	65	27	20		
120	M 24	-	-	-	-	100	125	150	200	300	-	-	-	-	-	-	-	-	-	-	-	-	-		
120	M 30	-	-	-	-	100	125	150	200	300	-	-	-	-	-	-	-	-	-	-	-	-	-		

* only available for the dimensions d₁ = 60, 80 and 100.

Specification

- Base plate
Stainless steel AISI 304
- Threaded stem
Stainless steel AISI 303
- Hex nut ISO 4032
Stainless steel AISI 304
- Rubber pad, inlaid
 - Black: NBR (Perbunan®)
80±5 Shore A
 - White: TPE (Santoprene®)
80±5 Shore A
- Rubber pad, vulcanized
 - 80±5 Shore A
 - Black: NBR (Perbunan®)
 - White: NBR (Perbunan®)
- RoHS

Versions of threaded stem

<p>S Without nut SK With nut</p>	<p>T Without nut TK With nut</p>	<p>U Without nut UK With nut</p>
<p>External hex at the bottom at d_2 M 8, M 10, M 12</p>	<p>Wrench flat at the bottom at d_2 M 16, M 20, M 24, M 30</p>	<p>Hex socket at the top and wrench flat at the bottom at d_2 M 16, M 20, M 24, M 30</p>

<p>V Without nut VK With nut</p>	<p>W With adjustable sleeve</p>	<p>X With internal thread</p>
<p>External hex at the top and wrench flat at the bottom at d_2 M 16, M 20, M 24</p>	<p>Covered thread and wrench flat at the bottom at d_2 M 16, M 20, M 24</p>	<p>External hex with internal thread at d_2 M 8, M 10, M 12, M 16, M 20</p>

d_1	d_2	d_3	h_1	h_2	$h_3 + 4$	$h_4 + 4$	$h_5 + 4$	l_4	l_5	l_6	s	A/F ₁	A/F ₂	A/F ₃	A/F ₄	A/F ₅	A/F ₆	
50	M 8 M 10 M 12	-	14,5	3,5	23	-	-	-	-	-	3	17	-	-	-	-	-	
50	M 16	-	14,5	3,5	-	29	-	-	-	-	3	-	12	8	-	-	-	
60	M 8 M 10 M 12	-	16	4	24	-	-	-	-	-	3	17	-	-	-	-	-	
60	M 16	-	24	16	4	-	30	27	45	45	29	3	-	12	8	10	12	20
80	M 8 M 10 M 12	-	18	5	26	-	-	-	-	-	3	17	-	-	-	-	-	
80	M 16	-	24	18	5	-	32	29	45	45	29	3	-	12	8	10	12	20
80	M 20	-	30	18	5	-	33	30	56	56	36	3	-	15	10	13	16	24
80	M 24	-	35	18	5	-	36	33	67	67	42	3	-	19	12	17	20	30
100	M 8 M 10 M 12	-	20	6	28	-	-	-	-	-	3	17	-	-	-	-	-	
100	M 16	-	24	20	6	-	34	31	45	45	29	3	-	12	8	10	12	20
100	M 20	-	30	20	6	-	35	32	56	56	36	3	-	15	10	13	16	24
100	M 24	-	35	20	6	-	38	35	67	67	42	3	-	19	12	17	20	30
120	M 20	-	22	6	-	39	-	-	-	-	4	-	15	10	-	-	-	
120	M 24	-	22	6	-	42	-	-	-	-	4	-	19	12	-	-	-	
120	M 30	-	22	6	-	46	-	-	-	-	4	-	24	12	-	-	-	

Information

Leveling feet GN 31 with vulcanised rubber (Types B3, B4, C3 and C4) and screw version W feature fewer dead spots owing to their construction method and are also easier to clean.

Leveling feet GN 31 will be delivered mounted and are not removable.

• [Load Rating Information](#) → Page 2143

see also...

- [Leveling Feet GN 33 \(with Mounting Flange\)](#) → Page 1482
- [Leveling Feet GN 30 \(Steel, Zinc Plated\)](#) → Page 1476

How to order

1	d_1
2	d_2
3	l_1 (l_2, l_3, l_7)
4	Type (Base plate)
5	Version (Stem)

GN 31-80-M20-100-C4-U