


Mounting clamp joint with clamping kit GN 511.1, type K



Clamping kit GN 511.1, type S



Rostfrei Inox Stainless Steel

3 Type

- A** With bore
- W** With bolt

1 1 2

d_1 Type A	d_2 Type W	k	d_3	d_4 Swivel bore	d_5	l_1	l_2	l_3	l_4	l_5	l_6	t	Clamping kit for d_4 Type S	Clamping kit for d_4 Type K
B 8	8	16	7	4,5	M 4	30	22	13	8	5,5	16	8		
B 10	10	20	8,5	5,5	M 5	38	28	17	10	7	17	10		
B 12	12	20	8,5	5,5	M 5	38	28	17	10	8	19	12		
B 15	15	25	10	6,5	M 6	46	33,5	20	12,5	10	21	15		
B 16	16	25	10	6,5	M 6	46	33,5	20	12,5	11	24	16		
B 20	20	30	10	6,5	M 6	55	40	24	15	12	26	18		

Specification

- Aluminum
 - Matte finish, tumbled **MT**
 - Anodized black **ELS**
- Bolt (Type W)
Stainless steel AISI 303
- Grub screw DIN 913 (Type A)
Stainless steel AISI 304
- Grub screw DIN 915 (Type W)
Stainless steel AISI 304
- *Stainless Steel characteristics* → Page 2166
- **RoHS**

Accessory

- Clamping Kits GN 511.1 → Page 1805

4

Information

T-swivel mounting clamps GN 483 can be combined with swivel mounting clamps GN 482, attachment swivel mounting clamps GN 484 as well as base plate swivel mounting clamps GN 485 with the same k dimensions to clamp connector joints. Clamping kits GN 511.1 with screw (type S) and with adjustable hand lever (type K) are available for this purpose. The article code for ordering is shown in the dimensional table.

see also...

- *Retaining Rods / Retaining Tubes GN 480.1* → Page 1833

How to order (With bore)

GN 483-B12-20-A-MT

- 1** d_1
- 2** k
- 3** Type
- 4** Finish

How to order (With bolt)

GN 483-20-30-W-ELS

- 1** d_1
- 2** k
- 3** Type
- 4** Finish