



d₁ Ø Insert	d₂ Thread	d₃H7 Bore with keyway	s₁ Square	s₂ Hexagon	b	d₄	d₅	h	Length l	max. torque in Nm			
12	M 8	-	V 8	-	22	9	20	11	118	40			
17	M 10	M 12	K 10	K 12	30	11	26	14	156	70			
22	M 14	M 16	K 14	K 16	V 12	V 14	SK 14	39,5	14	33	17	187	130
26	M 20	-	K 18	-	V 17	-	SK 17	46	17	33	22	219	180

Specification

Housing

Steel
Powder coated
Black matte, textured finish

Shaft

Stainless steel AISI 303
Matte shot-blasted

Wearing parts

Steel, hardened

Domed gear knob GN 719.1

Plastic, phenolic resin (PF)
Black, shiny finish

RoHS

On request

- Other inserts

Accessory

GN 184 Countersunk Washers
(for Axial Fixing)

Page

QVX

Ratchet spanners GN 316 are robust, easy to handle and have an appropriate and attractive design.

Ratchet spanners are normally used wherever the same ratchet insert is always required or where it makes sense to leave the ratchet spanner at the place of use or attach it to equipment or machinery as a „stationary“ tool. Various different versions of ratchet insert are available and these can be exchanged as required by loosening the retaining screw and removing the cover plate.

The ratchet action is deactivated when the reversing lever is in the locked position (central position), allowing torque to be applied in both directions.

see also...

GN 318 Ratchet Spanners (Stainless Steel)

Page

QVX

Technical Information

Keyways DIN 6885-1

QVX

Squares DIN 79

QVX

ISO Fundamental Tolerances

QVX

Stainless Steel Characteristics

QVX

How to order

GN 316-26-V17

1 d₁

2 s₁ (d₂, d₃, s₂)

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

