



4 Type (Base)

A1 Steel, zinc plated rubber inlaid, black

A5 Steel, plastic coated, black rubber inlaid, black

d ₁	d ₂	l ₁	Version S / SK								Version U / UK		l ₇ Version X	h ₁	l ₈	l ₉	
			40	50	63	-	-	-	-	-	-	-					75
50	M 8	8	40	50	63	-	-	-	-	-	-	-	-	40	18	25	45
50	M 10	5	50	60	80	100	-	-	-	-	-	-	43	18	25	45	
50	M 12	6	60	80	100	125	-	-	-	-	-	-	47	18	25	45	
50	M 16	-	-	-	-	-	75	100	125	150	200	250	52	18	25	45	
60	M 8	4	40	50	63	-	-	-	-	-	-	-	41	19	25	50	
60	M 10	5	50	60	80	100	-	-	-	-	-	-	44	19	25	50	
60	M 12	6	60	80	100	125	-	-	-	-	-	-	48	19	25	50	
60	M 16	-	-	-	-	-	75	100	125	150	200	250	53	19	25	50	
80	M 8	4	40	50	63	-	-	-	-	-	-	-	42	20	30	70	
80	M 10	5	50	60	80	100	-	-	-	-	-	-	45	20	30	70	
80	M 12	6	60	80	100	125	-	-	-	-	-	-	49	20	30	70	
80	M 16	-	-	-	-	-	75	100	125	150	200	250	54	20	30	70	
80	M 20	-	-	-	-	-	75	100	125	150	200	250	62	20	30	70	
80	M 24	-	-	-	-	-	100	125	150	200	300	-	-	20	30	70	
100	M 8	4	40	50	63	-	-	-	-	-	-	-	43	21	30	80	
100	M 10	5	50	60	80	100	-	-	-	-	-	-	46	21	30	80	
100	M 12	6	60	80	100	125	-	-	-	-	-	-	50	21	30	80	
100	M 16	-	-	-	-	-	75	100	125	150	200	250	55	21	30	80	
100	M 20	-	-	-	-	-	75	100	125	150	200	250	63	21	30	80	
100	M 24	-	-	-	-	-	100	125	150	200	300	-	-	21	30	80	

Specification

- Base plate, steel sheet metal
 - Type A1: Steel, zinc plated, blue passivated
 - Type A5: Steel, plastic coated black, RAL 9005
- Lug, sheet metal
 - Steel, zinc plated, blue passivated
- Threaded stem
 - Steel, zinc plated, blue passivated
- Hexagon nut ISO 4032
 - Steel, zinc plated, blue passivated
- Rubber pad, inlaid black, Perbunan® (NBR) 80±5 Shore A
 - Elastomer characteristics → Page 1483
 - Load rating information → Page 1471
 - RoHS

Versions of threaded stem

<p>S without nut SK with nut</p>	<p>U without nut UK with nut</p>	<p>X with female thread</p>
<p>External hexagon at the bottom at d_2 M 8, M 10, M 12</p>	<p>Hexagon socket at the top and wrench flat at the bottom at d_2 M 16, M 20, M 24</p>	<p>External hexagon with female thread at d_2 M 8, M 10, M 12, M 16, M 20</p>

d_1	d_2	h_3	h_4	A/F ₁	A/F ₂	A/F ₃	A/F ₇	t
50	M 8	26	-	17	-	-	14	8
50	M 10	26	-	17	-	-	14	10
50	M 12	26	-	17	-	-	17	12
50	M 16	-	32	-	12	8	22	16
60	M 8	27	-	17	-	-	14	8
60	M 10	27	-	17	-	-	14	10
60	M 12	27	-	17	-	-	17	12
60	M 16	-	33	-	12	8	22	16
80	M 8	28	-	17	-	-	14	8
80	M 10	28	-	17	-	-	14	10
80	M 12	28	-	17	-	-	17	12
80	M 16	-	34	-	12	8	22	16
80	M 20	-	35	-	15	10	27	20
80	M 24	-	38	-	19	12	-	-
100	M 8	29	-	17	-	-	14	8
100	M 10	29	-	17	-	-	14	10
100	M 12	29	-	17	-	-	17	12
100	M 16	-	35	-	12	8	22	16
100	M 20	-	36	-	15	10	27	20
100	M 24	-	39	-	19	12	-	-

Information

Levelling feet GN 32 will be delivered mounted and are not removable.

see also...

- *Stainless Steel-Levelling feet GN 33 (with fixing lug) → Page 1050*
- *Levelling feet GN 30 (Steel, zinc plated, without fixing lug) → Page 1044*

How to order		1	d_1
		2	d_2
		3	l_1 (l_7)
		4	Type (Base plate)
		5	Version (Stem)

GN 32-100-M20-150-A1-U