



ELESA Original design ME.

1.1  
1.2  
1.3  
1.4

<sup>1</sup> $l_1$	<sup>2</sup> $d_1$ H7 Bore	$d_2$	$b_1$	$b_2$	$h_1$	$h_2$	$h_3 \approx$	$l_2$	$t$ min.	$\varnothing$ Handle
65	B 8	13	19	22	18	23	40	23	13	18
80	B 10	14	20	24	20	26	40	30	16	18
95	B 10	14	22	26	22	29	50	36	19	21
110	B 12	18	22	28	24	34	65	44	18	23
140	B 12	18	24	30	26	37	80	57	18	26

**Specification**

- Body  
Plastic  
Duroplast (Phenolic PF)  
- reinforced  
- temperature resistant up to 110 °C  
- black, shiny finish
- Hub bushing  
Steel, blackened
- Threaded bushing to accept the revolving handle  
Brass
- Revolving handles GN 598  
- Plastic, Duroplast  
black, shiny finish  
- Spindle steel  
zinc plated, blue passivated
- ISO-Fundamental Tolerances → Page XYZ
- RoHS

**Information**

Cranked handles GN 510 allow fine adjustment.  
 These cranked handles are fitted to shaft with a cross pin. To simplify the installation there is a centred drilling on both sides.  
**see also...**  
 • Control handles GN 112.1 (Zinc die casting) → Page XYZ  
 • Tri-ball handles GN 10 (Steel, turned) → Page XYZ

2.1  
2.2  
2.3  
2.4

How to order <b>GN 510-80-B10</b>	<sup>1</sup> $l_1$
	<sup>2</sup> $d_1$