



- 3 Type**
- A** Mounting from the back (threaded blind bore)
 - B** Mounting from the operator's side (only for $d_1=28$)

d₁	Length l ±0,25								d₂	b₁	b₂	b₃	b₄	h₁	h₂	t min.
	180	200	250	300	350	400	500	600								
20	180	200	250	300	350	400	-	M 6	24	12	42	54	42	54	12	
28	200	250	300	350	400	500	600	M 8	25	14	50	66	50	66	15	
30	200	300	350	400	500	600	1000	M 8	27	17	51	68	51	68	15	

Specification

- Handle tube
Aluminum (wall thickness 1,5)
- Handle legs
Zinc die casting
- Tube ● **SW**
plastic coated
black, RAL 9005, textured finish
Handle legs plastic coated
black, RAL 9005, textured finish
- Tube, anodized, natural color ● **EL**
Handle legs plastic coated
black, RAL 9005, textured finish
- Tube, anodized, natural color ● **ES**
Handle legs plastic coated
silver, RAL 9006, textured finish
- Cover
Plastic, light gray
- Cover cap (Type B)
Plastic (Technopolymer)
- black (for SW / EL)
- light gray (for ES)
- Load rating information → Page 1450
- RoHS

Information

The handle tube of the GN 333 tubular handles can be screwed to the handle bases without further machining or processing, allowing **special lengths** to be realised easily.

A typical application area for tubular handles GN 333 are double-winged doors at machines or devices.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles Ø 28 (type A) are available under GN 333.8 → Page 135.

see also...

- Product family Standard Parts for profile systems → Page 20
- Tubular handles GN 333.1 (straight) → Page 130
- Tubular handles GN 332 (with power switching function) → Page 138
- Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
- Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

How to order

GN 333-28-600-A-EL

1	d₁
2	Length l
3	Type
4	Finish