



3 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side (only for $d_1=28$)



1 **2**

d_1	Length $l \pm 0,25$								d_2	b_1	b_2	b_3	b_4	h_1	h_2	t min.
20	180	200	250	300	350	400	-	M 6	24	12	42	54	42	54	12	
28	200	250	300	350	400	500	600	M 8	25	14	50	66	50	66	15	
30	200	300	350	400	500	600	1000	M 8	27	17	51	68	51	68	15	

Specification

- Handle tube
Aluminum (wall thickness 1,5)
- Handle legs
Zinc die casting
- Tube plastic coated **SW**
black, RAL 9005, textured finish
Handle legs plastic coated
black, RAL 9005, textured finish
- Tube, anodized, natural color **EL**
Handle legs plastic coated
black, RAL 9005, textured finish
- Tube, anodized, natural color **ES**
Handle legs plastic coated
silver, RAL 9006, textured finish
- Cover
Plastic, light gray
- Cover cap (Type B)
Plastic (Technopolymer)
black (for SW / EL)
light gray (for ES)
- Load rating information → Page 1450
- RoHS

Information

- The handle tube of the GN 333 tubular handles can be screwed to the handle bases without further machining or processing, allowing **special lengths** to be realised easily.
- A typical application area for tubular handles GN 333 are double-winged doors at machines or devices.
- Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles $\varnothing 28$ (type A) are available under GN 333.8 → Page 135.
- see also...
- Product family Standard Parts for profile systems → Page 20
 - Tubular handles GN 333.1 (straight) → Page 130
 - Tubular handles GN 332 (with power switching function) → Page 138
 - Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
 - Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

How to order

GN 333-28-600-A-EL

1	d_1
2	Length l
3	Type
4	Finish