



3 Type

A Mounting from the back (threaded blind bore)

1 d_1	2 Length l	d_2	b_1	b_2	b_3	b_4	h_1	h_2	$t_{min.}$
28	242 292 392 492 592	M 8	25	14	50	66	50	66	15

Specification

Handle tube

Aluminum, wall thickness 1,5 mm

- Powder coated
Black, RAL 9005, textured finish
- Anodized, natural color
- Anodized, natural color
- Silver, RAL 9006 for ELG

- **SW**
- **ELS**
- **ELG**

Handle legs

- Zinc die casting
- Powder coated, textured finish
- Black, RAL 9005 for SW / ELS
- Silver, RAL 9006 for ELG

Cover

- Plastic
- Black, matte finish for SW / ELS
- Light gray, matte finish for ELG

RoHS

On request

- Special lengths

The spacing of the attachment holes of the tubular handles GN 333.2 is adjustable.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles \varnothing 28 (type A) are available under GN 333.8. Tubular handles GN 333.2 are supplied unassembled.

see also...

	Page
GN 333 Tubular Handles (with Fixed Handle Legs)	QVX
GN 333.3 Tubular Handles (Straight, with Movable Handle Legs)	QVX
GN 930 Handle Tubes	QVX

Technical Information

Load Rating Information	QVX
-------------------------	-----

Accessory

GN 333.8 Handle Legs	QVX
-----------------------------	-----

How to order

1 d_1
2 Length l
3 Type
4 Finish

GN 333.2-28-492-A-SW