




Original design I.280

1

2

d ₁	d ₂	d ₃	l ₁	l ₂ min.	l ₃ ±0,5
14	M 5	11	28	12	1,5
18	M 6	15	40	25	3,5
18	M 8	15	40	25	3,5
21	M 6	17	50	25	3,5
21	M 8	17	50	35	7,5
23	M 8	19	65	30	7,5
23	M 10	19	65	40	7,5
26	M 8	21	80	45	7
26	M 10	21	80	55	7
26	M 12	21	80	55	10
28	M 8	22	90	45	7
28	M 10	22	90	55	7
28	M 12	22	90	58	8
29	M 12	23	116	58	8
31	M 12	25	102	58	8

Specification

Plastic, phenolic resin (PF)

- Operating temperature -20 °C to +110 °C
- Black, shiny finish

RoHS

When using the cylindrical knobs GN 519, make sure that the threaded pin is not too short. Otherwise the plastic element may break under excessive stress exposure.

Technical Information

Plastic Characteristics

Page

QVX

How to order


1 d₁2 d₂