



¹ d ₁	² d ₂ Bore		d ₃	l ₁	l ₂ min.
18	B 8	-	15	40	28
21	B 10	-	17	50	35
23	B 10	B 12	19	65	45
26	B 12	B 14	21	80	50
28	B 15	B 16	22	90	60

Specification

- Plastic Technopolymer (Polypropylene PP)
 - Shock resistant
 - Temperature resistant up to 80 °C
 - Black, matte finish
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

Information

The cylindrical knobs GN 519.1 do not require a thread at the shaft. During mounting, easy blows with a soft hammer are sufficient to drive the knob into place, the shaft end should be slightly rounded or chamfered (30°). The knobs sit absolute vibration-tight.

see also...

- Softline Handle GN 819 (Press-On Type) → Page 74

How to order GN 519.1-26-B12	¹ d ₁
	² d ₂