



**Rost frei**®  
Inox  
Stainless  
Steel

**4 Type**


- A** without lock nut
- B** with lock nut



**1**

**2**

**3**

d <sub>1</sub> Support plate d <sub>1</sub> = d <sub>4</sub>   d <sub>1</sub> > d <sub>4</sub>	d <sub>2</sub>	h <sub>1</sub> max.	d <sub>3</sub>	d <sub>4</sub>	h <sub>2</sub> min.	h <sub>3</sub> Adjustable range	h <sub>4</sub> min.	h <sub>5</sub> Adjustable range	Static load F in kN		Code no. C-Spanner 	
									ST	NI		
40	79	M 10	69	M 28 x 1,5	40	53	16	59	10	100	70	DIN 1810-A40-42
40	79	M 10	86	M 28 x 1,5	40	62	24	68	18	100	70	DIN 1810-A40-42
52	99	M 12	80	M 36 x 1,5	52	61	19	69	11	125	85	DIN 1810-A52-55
52	99	M 12	103	M 36 x 1,5	52	73	30	80	23	125	85	DIN 1810-A52-55
65	119	M 16	112	M 45 x 1,5	65	82	30	90	22	225	155	DIN 1810-A65-70
65	119	M 16	148	M 45 x 1,5	65	100	48	108	40	225	155	DIN 1810-A65-70

**Specification**

- Steel **ST**  
zinc plated, blue passivated
- Stainless Steel AISI 304 **NI**
- *Stainless Steel characteristics* → Page 1489
- RoHS

**Accessory**

- C-Spanner DIN 1810  
(code no. see table)

**Information**

GN 360 levelling sets are used for leveling and to compensate for any slope when setting up machines and systems.

The thread d<sub>2</sub> can also be used as a through-hole for attachment from below. The fine thread d<sub>3</sub> laws precise adjustment and readjustment using a DIN 1810 C-Spanner. A circlip limits the maximum path of adjustment.

see also...

- *Levelling sets GN 350 / GN 350.1* → Page 850 / 851
- *Levelling sets GN 350.2 / GN 350.5* → Page 852 / 853

**How to order**

<b>1</b>	d <sub>1</sub>
<b>2</b>	d <sub>2</sub>
<b>3</b>	h <sub>1</sub>
<b>4</b>	Type
<b>5</b>	Material

**GN360-119-M16-148-A-ST**

