



ELESA Original design VRTP./VRTP+I



2 Bore code

- B** without keyway
- K** with keyway

4 Type

- A** without handle
- R** with revolving handle

1

3

| d ₁ | d ₂ H7 Bore | d ₃ | d ₄ | d ₅ | b | l ₁ | l ₂ | l ₃ | r | Ø Handle |
|----------------|------------------------|----------------|----------------|----------------|------|----------------|----------------|----------------|-----|----------|
| 80 | 8 | 10 | 18 | 20,5 | 25 | 18 | 17 | 35 | 29 | 16 |
| 100 | 10 | 12 | 18 | 20,5 | 25,5 | 20 | 17 | 37 | 37 | 18 |
| 125 | 12 | 14 | 22 | 26 | 31 | 22 | 22 | 44 | 48 | 22 |
| 160 | 14 | 16 | 26 | 31 | 40 | 25 | 27 | 51 | 65 | 23 |
| 200 | 16 | 20 | 30 | 36 | 48,5 | 28 | 34 | 61 | 84 | 24 |
| 250 | 20 | 24 | 35 | 44 | 58 | 32 | 38 | 69 | 105 | 25 |
| 300 | 20 | 26 | 40 | 52 | 66 | 35,5 | 43 | 78 | 127 | 25 |
| 375* | 26 | - | 35 | 70 | 81 | 39 | 43 | 87 | 160 | 25 |

* not available from stock, requires a minimum order quantity

Specification

- Plastic Technopolymer (Polypropylene PP)
 - reinforced, shock-resistant
 - temperature resistant up to 80 °C
 - black, matte
- Hub bushing Steel, blackened
- Threaded bushing Brass
- Revolving handles
 - Plastic, Technopolymer (Polyamide PA) black, matte
 - Spindle steel zinc plated, blue passivated
- Keyway P9 DIN 6885 → Page 1420
- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- Plastic characteristics → Page 1483
- RoHS

Information

Elegant design and ergonomic requirements are realised for the spoked handwheels GN 522.

see also...

- Countersunk washers GN 184 (for axial fixing) → Page 814

How to order

GN 522-125-B 12-R

| | |
|----------|----------------|
| 1 | d ₁ |
| 2 | Bore code |
| 3 | d ₂ |
| 4 | Type |