



elesa
Original design VDT.



- 2 Bore code**
B Without keyway
K With keyway DIN 6885-1 P9
- 4 Type**
A Without handle
D With revolving handle

| d₁ | d₂ H7 Bore | b | d₃ | d₄ | d₅ | d₆ | h | l₁ -0,5 | l₂ -0,5 | l₃ | r | Ø Handle |
|----------------------|------------------------------|----------|----------------------|----------------------|----------------------|----------------------|----------|---------------------------|---------------------------|----------------------|----------|-----------------|
| 100 | 10 | 22 | 22 | 20 | 25 | 32 | 5,5 | 22 | 49 | 60 | 37 | 18 |
| 125 | 12 | 25 | 26 | 24 | 29 | 37 | 7 | 27 | 58 | 65 | 47 | 22 |
| 160 | 14 | 27 | 35 | 33 | 37 | 46 | 11 | 28 | 64 | 80 | 62 | 24 |
| 200 | 20 | 30 | 40 | 38 | 48,5 | 51 | 9 | 31 | 67 | 90 | 78 | 25 |

Specification

Wheel body

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature 0 °C to +80 °C
- Black, matte finish

Hub bushing

Steel, blackened

Threaded bushing

Brass

Cover

Black, matte finish

Revolving handle

- Plastic, Polyamide (PA)
- Black, matte finish
- Spindle steel
- Zinc plated, blue passivated

RoHS

Disk handwheels GN 524 are renowned in particular for their design and the matte passivated aluminum ring.

The cover shrouds the fixing components such as screws, countersunk washers as well as the shaft end. The cover is inserted by pushing it on by hand. To remove it run a finger with little pressure along the edge of the cap.

see also...

| | Page |
|--|-------------|
| GN 521 Disk Handwheels (Polypropylene) | QVX |
| GN 520.1 Disk Handwheels (Phenolic Resin) | QVX |

Technical Information

| | |
|----------------------------|-----|
| Keyways DIN 6885-1 | QVX |
| Cross holes GN 110 | QVX |
| ISO Fundamental Tolerances | QVX |
| Plastic Characteristics | QVX |

Accessory

| | |
|---|-----|
| GN 184 Countersunk Washers (for Axial Fastening) | QVX |
|---|-----|

How to order

GN 524-125-B12-D

- 1** d₁
- 2** Bore code
- 3** d₂
- 4** Type