



Assembly set
GN 965 / GN 968

1

2

d		b ₁	b ₂	b ₃	b ₄	h ₁	h ₂	k ₁	k ₂	k ₃
Nominal dimension	Actual dimension <small>+0.15 -0.05</small>									
6	6,2	38	32	16	5,4	8,5	6	27	5,5	21
8	8,2	38	32	16	5,4	8,5	6	27	5,5	21
8	8,2	46	40	20	6,4	11	6	33	6,5	27
10	10,2	38	32	16	5,4	8,5	6	27	5,5	21
10	10,2	46	40	20	6,4	11	6	33	6,5	27
12	12,2	46	40	20	6,4	11	6	33	6,5	27

Specification

- Zinc die casting
Powder coated
Black, RAL 9005, textured finish
- RoHS

Information

Locators GN 416.1 are matched to the spring latches GN 416 and are used to position the plunger pin.

see also...

- *Product Family Standard Parts for Profile Systems* → Page 18
- *Spring Latches GN 416 (with and without Rest Position)* → Page 930
- *Assembly Sets for Profile Systems 30 / 40 GN 965* → Page 2086
- *Assembly Sets for Profile Systems 30 / 40 / 45 GN 968* → Page 2096

How to order

GN 416.1-8-46

1 d

2 b₁