



ELESA Original design IZN.380

1 d_1 f7	2 d_2 H7 Bore	d_3	d_4	d_5	d_6	d_7	l_1	l_2	l_3	l_4	l_5	r	
32	B 6	-	15	19	21	3	-	26	5	16	8	9	-
37	B 6	-	15	25	27	3	-	29	6	16	10	10	-
42	B 8	-	18	29	31	4	-	32	7	17	11	11	-
48	B 8	-	22	32	34	4	3,2	35	8	22	10	14	14
52	B 10	B 12	22	37	39	4	4,2	39	9	22	13	14	15
58	B 12	-	26	42	44	5	5,2	41	10	27	11	16	17
63	B 12	B 14	26	48	50	5	6,2	44	11	30	10	16	19
80	B 16	-	26	59	62	5	6,2	48	12	30	13	17	24

Specification

- Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black, shiny finish
- Bushing
Steel, blackened
- Cover
Plastic, light gray
- ISO-Fundamental tolerances → Page 1479
- Plastic characteristics → Page 1483
- RoHS

Information

The light gray cover of the control knobs GN 526 shrouds the fixing components as well as the shaft end. The cover also lends itself for a logo or other symbols.

The cap is mounted by simply pressing it by hand into place. To remove it run the finger with some pressure along its rim.

see also...

- Scale rings GN 526.1 (for GN 526) → Page 258
- Control knobs GN 726 (Aluminum) → Page 259
- Control knobs GN 726.1 (Aluminum) → Page 260
- Clamping elements GN 826 (for adjustable spindles) → Page 268

How to order

GN 526-42-B8

1 d_1

2 d_2